



[Back to Result](#)

JP2WP2B-L20 [Add to BOM](#) | [Add to Favorites](#)



J-Hook for powder actuated installation on walls. One 5/32" (M4) mounting hole and one 1/4" (M6) mounting hole for user supplied fasteners.

Product Details | Related Documents

Std. Pkg. Qty.	50
Std. Pallet Volume (cf)	0.000000
Std. Pallet Weight (lb)	272.8765
Std. Ctn. Volume (cf)	0.0000
Std. Ctn. Weight (lb)	0.0000
RoHS Compliancy Status	Compliant
Part Description	J-Hook for powder actuated installation on walls. One 5/32" (M4) mounting hole and one 1/4" (M6) mounting hole for user supplied fasteners.
Max. Bundle Capacity (mm)	50.8
Max. Static Load (Kg)	13.61
Max. Bundle Capacity (In.)	2.00
CE Compliant	No
Part Features	Bend Radius Control, Smooth Pulling Surface
Application	Route high performance communication cabling in air handling spaces
Product Type	J-Pro Cable Support
Max. Static Load (Lbs)	30
Material	Nylon 6.6 with metal attachments
Color	Black
Pricing Description	J-Pro Cable Support System Wall Mount With Bracket, Black
CAT 5E (.193")	55
CAT 6 (.248")	46
10Gig (.33")	28
Model (Design)	Wall Mount with Bracket
BMEcat - Mounting Method	Wall/ceiling/suspension
BMEcat - Model	Mbunting Bracket
Min. Order Qty.	50.0000