

# Han-Eco 10B-HTE-for DL-M20



| Part number        | 19 43 010 0425                      |
|--------------------|-------------------------------------|
| Specification      | Han-Eco 10B-HTE-for DL-M20          |
| HARTING eCatalogue | https://b2b.harting.com/19430100425 |

#### Identification

| Category                            | Hoods/Housings |
|-------------------------------------|----------------|
| Series of hoods/housings Han-Eco® B |                |
| Type of hood/housing                | Hoods          |

#### Version

| Locking type | Double locking lever |
|--------------|----------------------|
| Size         | 10 B                 |
| Version      | Top entry            |
| Cable entry  | 1x M20               |

#### Technical characteristics

| Limiting temperature                   | -40 +125 °C |
|--|-------------|
| Number of relockings                   | ≥500        |
| Degree of protection acc. to IEC 60529 | IP66        |

### Material properties

| Material (hood/housing)                   | Polyamide Fibre-glass reinforced |
|---|----------------------------------|
| Colour (hood/housing)                     | RAL 9005 (jet black)             |
| Material flammability class acc. to UL 94 | V-0                              |

# Specifications and approvals

|                | IEC 61984                     |
|----------------|-------------------------------|
| Charifications | EN 45545-2 R22: HL1, HL2, HL3 |
| Specifications | EN 45545-2 R23: HL1, HL2, HL3 |
|                | EN 45545-2 R24: HL1, HL2, HL3 |
|                |                               |

#### Commercial data

| Packaging size | 1     |
|----------------|-------|
| Net weight     | 107 g |

Product data sheet 19 43 010 0425 Han-Eco 10B-HTE-for DL-M20



# Commercial data

| Country of origin              | Germany  |
|--------------------------------|----------|
| European customs tariff number | 85389099 |