


Soft Shell Connectors Soft Shell - Housings, Test Connectors and IDC Connectors Sales

9, 12 and 15 Circuit, Matrix



Line art represents typical product only.

Panel Cutout

Searchable Features:	
Product Type	Housing
Connector Line	Universal MATE-N-LOK
Contact Diameter	.084 [2.13] in. [mm]
Centerline	.250 x .250 [6.35 x 6.35] in. [mm]
# of Circuits	9
Contact Layout	Matrix
Mating Type	Сар
Mount	Free or Panel
Packaging Method	One Piece Housing
Housing Material	Nylon
Color	White
Lock Type	Positive Lock
Other Properties:	
Dim. A	.800 [20.32] in. [mm]
Dim. A (Panel Cutout)	.815 [20.70] in. [mm]
Dim. B (Panel Cutout)	.480 [12.19] in. [mm]
Dim. C (Panel Cutout)	.275 [6.99] in. [mm]
Dim. D (Panel Cutout)	1.030 [26.16] in. [mm]
Dim. E (Panel Cutout)	.250 [6.35] in. [mm]
Housing Flammability Rating	UL 94V-0

[<u>Main Menu</u> | <u>Help</u> | <u>Families</u> | <u>Registration</u> | <u>Feedback</u>] <u>Top of Page</u>