


440.3/8 440 - Inch combination wrenches



- Standard wrench for all current applications.
- High mechanical strength combined with compact size meeting aeronautical standards.
- Ring head:
 - Ring open end (size E) designed for better access to series or embedded screws.
 - OGV® profile with 12-point ring for powerful tightening while protecting the nut. H suffix = 6-point ring.
 - Ring head angled at 15°.
- Open end head:
 - Open end angled at 15°.
 - Open end head-handle geometry optimised for increased access.
- Dimensions in inches: from 1/4" to 1 1/2".
- Presentation: satin chrome finish.

A ["]: 3/8

B [mm]: 23,0

B1 [mm]: 15,0

C1 [mm]: 7,6

E [mm]: 4,2

E maxi [mm]: 4,2

E1 [mm]: 7,6

E2 [mm]: 5,2

L [mm]: 145

[g]: 45