



- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERM. NOS. FOR REFERENCE ONLY.
 4. RATING: 4A @125VAC, 2A @250VAC
 5. CONTACT RESISTANCE: 10mILLI-OHMS
 6. DIELECTRIC STRENGTH: 1500 VAC-1Minute
 7. INSULATION RESISTANCE: 200 Mega-OHMS
 8. MATERIALS:
HOUSING: ZINC ALLOY DIE CAST
CYLINDER: ZINC ALLOY W/CHROME PLATE
CONTACTS: SILVER PLATE
CRISS CROSS TUMBLERS. (11 BLADE)
DOUBLE BITTED KEYS (2) STAMPED 2007
 9. KEYLOCK, KEYS, AND HEX NUT TO BE PACKED TOGETHER IN INDIVIDUAL BAGS.

LEGEND

- = INDICATE NO KEY PULL
- ⊙ = INDICATES KEY PULL POSSIBLE

REV.	ECN NO.	DESCRIPTION	DATE	CHKD
C	18008	ADD NOTE 9	3/12/08	RC
B	12872	REMOVE TERM /NOTE 8	3/4/03	CJB
A	11402	RELEASED FOR PRODUCTION	4/10/01	RJC

ADD NOTE 9	3/12/08	RC	TITLE	SCALE	DATE	DR	DWG	REV
REMOVE TERM /NOTE 8	3/4/03	CJB	E-SWITCH® K0128A-2007	1.5:1	4/10/01	RJC	K200201	C
RELEASED FOR PRODUCTION	4/10/01	RJC						
DESCRIPTION	DATE	CHKD						

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KO128A2007](#)