




4812

4812

STAINLESS STEEL BALL VALVE DOUBLE FEMALE 1
PIECE


Maximum pressure depends on the working pressure and diameter of passage.

working temperature	°C (Celsius)	F (Fahrenheit)	K (Kelvin)
		From -20 to 160	From -4 to 320
body	stainless steel 316L		
retaining nut	stainless steel		
stem	stainless steel 316L		
stem seal	PTFE		
ball seal	PTFE		
handle	stainless steel 304L		
gripping ring	stainless steel		
screw	stainless steel		



4812
 STAINLESS STEEL BALL VALVE DOUBLE
 FEMALE 1 PIECE
 for metric tubing

4812

Part No	ØD (mm)	C	E (mm)	H (mm)	L (mm)	M (mm)	N (mm)	Z (mm)	 (kg)
4812 10 13	5,5	G1/4	10,0	50,0	55,0	110,0	36,0	36,0	0,263
4812 10 17	5,5	G3/8	11,4	50,0	55,0	110,0	36,0	36,0	0,232
4812 15 21	5,5	G1/2	15,0	53,0	66,0	110,0	36,0	36,0	0,328
4812 20 27	5,5	G3/4	16,3	67,0	79,0	130,0	42,0	42,0	0,574
4812 25 34	5,5	G1	19,1	79,0	93,0	175,0	42,0	42,0	1,000
4812 32 42	5,5	G1 1/4	21,4	83,0	100,0	175,0	42,0	42,0	1,337
4812 40 49	5,5	G1 1/2	21,4	100,0	110,0	250,0	50,0	50,0	2,028
4812 50 48	8,5	G2	25,7	107,0	131,0	250,0	70,0	70,0	3,262