

NingBo FBELE Electronics Co., Ltd

Model	FBS5090-80HM
Dimension	Outer Diameter50-90mm Baffle Opening35mm Height Refer to drawing in details;
Nominal Impedance	8 Ohm±15% At1000 HZ
Power Rating	5 watt Maximum 6 Watt
Lowest Resonant Frequency	350±20% HZ.
Output Sound Pressure Level (S. P. L)	86 ±3db/1 Watt. 1Meter. Average at 800, 1000, 1200, 1500 HZ.
Frequency Range	FO-18 KHZ , Average SPL±10db
Distortion	3%Maximum At1000HZ 5 W
Polarity	Diaphragm shall move forward when Apply a Postive DC current the "+" or "Marked" Terminal
Load Test	Bt Audio Singnal Generator At 4.47 Volts. total 48 hours and20~20KHZ Resonant Frequency
Abnormal Sound Test	Must be Normally tested Bt 4.47 Volts Sinwave
Operation Temperature	- 20°C ~ + 50°C
Storage Temperature	- 40°C ~ + 60°C

