



Fuse-link, high speed, 100 A, AC 690 V, 200 kA, DIN 000, 21 x 40 x 100 mm, aR, DIN, IEC, single indicator



Part no. FUSE 100A 690V 000/80 AR UC
 Catalog No. 170M1367

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	100
Rated voltage			AC 690 V
Construction size			DIN 000
Size			21 x 40 x 100 mm
Utilization category			aR
Status indicator			single indicator
Breaking Capacity		kA	200
usable for size/applications			semiconductor protection
Standard/Approval			DIN IEC
Shape			square body with offset bolted tags (slotted)
Standards/Regulations			DIN 43653 IEC 60269-4

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / HRC fuse (EC004556)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Safety fuse inserts (unspecified) (ecl@ss10.0.1-27-14-20-90 [BAB264011])			
Fuse construction type according to IEC 60269			Other
Type of current			
Rated voltage AC		V	690
Rated voltage DC		V	
Rated current		A	100
Utilization category			aR (accompanied semiconductor protection)
Breaking capacity		kA	
Colour code			
Type of fuse status indicator			Top fuse status indicator
Power loss at rated current		W	24
Mounting holes			
Centre-to-centre distance of connections		mm	

Additional product information (links)

Product datasheet (pdf)	http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/product-datasheets-b/Bus_Ele_DS_720013_170M.pdf
-------------------------	---