



## Deep groove ball bearings, single row, seal on both sides

Principal dimensions			Basic load ratings		Fatigue load limit $P_u$	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
7	19	6	2,34	0,95	0,04	-	24000	0,0075	607-2RSH *



### Calculation factors

$k_r = 0,025$

$f_0 = 13$