

You are here: Products » Heatsinks f.cool » Profile heatsinks and fluid coolers » Standard extruded heatsinks » SK 04 ... » SK 04

Heatsinks f.cool

- ▼ Profile heatsinks and fluid coolers
 - Standard extruded heatsinks
 - Extruded heatsinks for lock-in retaining spring
 - Extruded heatsinks for PCB mounting
 - Extruded heatsinks for DC/DC converter
 - Retaining springs for transistors
 - U-Extruded heatsinks
 - Die-cast heatsinks
 - Fin coolers
 - Fluid coolers
 - Aluminium flat-, quadrangular-, angled-, U- & T-profiles
- ▶ Heatsinks and active heatsinks for processors
- ▶ Finger-shaped heatsinks
- ▶ Cooling aggregates
- ▶ Accessories for electronic components
- ▶ Cases f.case
- ▶ Connectors f.con

Standard extruded heatsinks

SK 04 50 SA

97 x 25 mm, with guideway for cover plates or blanks

add to request



Features Technical Drawing Service

width	97 mm
height	25 mm
plate thickness	4 mm
lengths	100 mm
R _{max}	1.3 - 2.8 K/W
drilling pattern	TO 3 CB SSR 1 SSR 2
surface	black anodised