

General Information

Extended Product Type: ZS4-S

 Product ID:
 1SNK505310R0000

 EAN:
 3472595053100

Catalog Description: ZS4-S Screw Clamp Terminal Block - Disconnect with blade - Grey

Long Description: - Ease your disconnect operations with the disconnect blade operated by hand or with a

screwdriver, - Same profile as ZS4 feed-through terminal block for aligned marking and

identical end section use.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » SNK Series

Ordering

Minimum Order Quantity:50 pieceCustoms Tariff Number:85369010Color:Grey

Dimensions

Product Net Height:53 mmProduct Net Length:51.35 mmProduct Net Depth:51.4 mmProduct Net Weight:8.6 gProduct Net Width:5.2 mm

Technical

Spacing:5.2 mmConnection Type:Screw clampFunction:Disconnect

Number of Levels:

Connecting Capacity Main Circuit: Screw Clamp / Flexible 1x 0.2 ... 4 mm²

Screw Clamp / Flexible 2x 0.2 ... 1.5 mm² Screw Clamp / Rigid 1x 0.2 ... 4 mm² Screw Clamp / Rigid 2x 0.2 ... 1.5 mm²

Screw Clamp / With Insulated Ferrule 1x 0.22 ... 2.5 mm² Screw Clamp / Without Insulated Ferrule 1x 0.22 ... 4 mm² Screw Clamp / With Twin Ferrule 2x 0.22 ... 1.5 mm²

Gauge Type: A3-B3

Rated Current (I_n): Main Circuit 25 A

Rated Short-time Withstand Current for 1 s 480 A

(I_{CW}):

Rated Voltage (U_r): 400 VRated Impulse Withstand Voltage 6000 V

(U_{imp}):

Dielectric Test Voltage: 1890 V
Pollution Degree: 3
Power Loss: 0.8 W

Degree of Protection: acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20

Insulation Material: Polyamide

Mounting on DIN Rail: TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Wire Stripping Length: 10.5 mm
Recommended Screw Driver: 3.5 mm
Rated Cross-Section: 4 mm²

Technical UL/CSA

Connecting Capacity Main Circuit

UL/CSA:

Screw Clamp / Flexible 1x 24 ... 10 AWG Screw Clamp / Flexible 2x 24 ... 16 AWG Screw Clamp / Rigid 1x 24 ... 10 AWG Screw Clamp / Rigid 2x 24 ... 16 AWG

Screw Clamp / With Insulated Ferrule 1x 24 ... 14 AWG Screw Clamp / Without Insulated Ferrule 1x 24 ... 10 AWG Screw Clamp / With Twin Ferrule 2x 24 ... 16 AWG

Connecting Capacity UL/CSA:

Stranded 10 AWG

Flammability According to UL94:

VC

Maximum Operating Voltage UL/CSA:

Main Circuit 150 V

Environmental

Resistance to Vibrations acc. to IEC Compliant

60068-2-6:

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Operation -55 ... +110 °C Storage -55 ... +110 °C **Ambient Air Temperature:**

Certificates and Declarations (Document Number)

1SNK160027C0201
1SND161073A0203
1SND161078A0200
1SND161070A0208
1SND161040A0206
1SNK161010D0201
1SND225102U1000
1SND161087A0202
1SND161009A1100
1SND161088A0200
1SND230491F0206

Classifications

E-nummer:	2925915
ETIM 4:	EC000902 - (Knife) disconnect terminal block
ETIM 5:	EC000902 - (Knife) disconnect terminal block
ETIM 6:	EC000902 - (Knife) disconnect terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	54 mm
Package Level 1 Length:	252 mm
Package Level 1 Height:	52 mm
Package Level 1 Gross Weight:	0.43 kg
Package Level 1 EAN:	3472595053100
Package Level 2 Units:	900 piece
Package Level 2 Width:	300 mm
Package Level 2 Length:	400 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	8.240 kg
Package Level 3 Units:	43200 piece
Product Packing Type:	Box
Package Level 1 Units:	50 piece

