



# Deep groove ball bearings, single row, seal on both sides



Principal dimensions			Basic load ratings		Fatigue load limit $P_u$	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
6	19	6	2,34	0,95	0,04	-	24000	0,0084	626-2RSH *



### Calculation factors

$k_r$  0,025

$f_0$  13