

G236



Assortment

Code	Short Description	Nr.	A	B	C
G2361	Set 1 (G136 x 6)	1	G136	6	6.30 mm, 8.30 mm, 10.40 mm, 12.40 mm, 16.50 mm, 20.50 mm
G2362	Set 2 (G136 x 4)	2	G136	4	6.30 mm, 10.40 mm, 16.50 mm, 20.50 mm
G2363	Set 3 (G560 x 6)	3	G560	6	6.30 mm, 8.30 mm, 10.40 mm, 12.40 mm, 16.50 mm, 20.50 mm

Tool Header Informations

G136

Countersink - 90°




- 1.1
- 1.2
- 1.3
- 1.4
- 1.5
- 4.1
- 4.2
- 4.3
- 5.1
- 5.2
- 5.3
- 6.1
- 6.2
- 6.3
- 1.6
- 2.1
- 2.2
- 2.3
- 3.1
- 3.2
- 3.3
- 3.4
- 6.4
- 7.1
- 7.2
- 7.3
- 7.4
- 8.1
- 8.2

max d mm	min d	l ₁ mm	d ₂ Øh ₉ mm	z	e-Code	GBP
4.3	1.3	40	4	3	G1364.3	27.10
5.0	1.5	40	4	3	G1365.0	24.85
5.3	1.5	40	4	3	G1365.3	27.00
5.8	1.5	45	5	3	G1365.8	29.60
6.0	1.5	45	5	3	G1366.0	26.20
6.3	1.5	45	5	3	G1366.3	28.40
7.0	1.8	50	6	3	G1367.0	29.05
7.3	1.8	50	6	3	G1367.3	26.30
8.0	2.0	50	6	3	G1368.0	31.30
8.3	2.0	50	6	3	G1368.3	29.85
9.4	2.2	50	6	3	G1369.4	28.90
10.0	2.5	50	6	3	G13610.0	36.30
10.4	2.5	50	6	3	G13610.4	34.25
11.5	2.8	56	8	3	G13611.5	35.30
12.4	2.8	56	8	3	G13612.4	38.60
13.4	2.9	56	8	3	G13613.4	38.85
15.0	3.2	60	10	3	G13615.0	43.30
16.5	3.2	60	10	3	G13616.5	48.50
19.0	3.5	63	10	3	G13619.0	56.40
20.5	3.5	63	10	3	G13620.5	65.80
23.0	3.8	67	10	3	G13623.0	72.70
25.0	3.8	67	10	3	G13625.0	95.30
26.0	3.8	67	10	3	G13626.0	102.00
28.0	4.0	71	12	3	G13628.0	118.00
30.0	4.2	71	12	3	G13630.0	138.00
31.0	4.2	71	12	3	G13631.0	139.00

G560

Countersink - 90°



max d mm	min d	l ₁ mm	d ₂ Øh ₉ mm	z	e-code	GBP
6.3	1.5	45	5	3	G5606.3	42.50
8.0	2.0	50	6	3	G5608.0	46.90
8.3	2.0	50	6	3	G5608.3	44.75
10.0	2.5	50	6	3	G56010.0	54.50
10.4	2.5	50	6	3	G56010.4	51.40
12.4	2.8	56	8	3	G56012.4	57.90
16.5	3.2	60	10	3	G56016.5	72.70
20.5	3.5	63	10	3	G56020.5	92.00
25.0	3.8	67	10	3	G56025.0	133.00
31.0	4.2	71	12	3	G56031.0	196.00