

## 27102 OSH

- Part number : 27102 OSH
- Body : Composite
- Nozzle : Composite
- Triger : Progressive
- Insert : 1/4 BSP female metal thread
- Maxi temperature : +70°C
- Mini temperature : -15°C
- Impossible dust intrusion
- Venturi high flow blowing
- Non scratch body
- Crush resistant
- Flow @ 6 b : 13 m3/h - 8.5 cfm
- Sound level : 90 db
- Nozzle lenght : 61 mm - 2.4 in
- Blowing force : 227 g
- Dynamic pressure : 2.5 b
- Weight : 116 g
- 

