




0439 - DOUBLE FEMALE WITH VENT BSPP



maximum working pressure	40 bar 4 MPa 580 psi
working temperature	-20 to 80 °C -4 to 176 °F 253 to 353 °K
body	NICKEL PLATED BRASS
retaining nut	NICKEL PLATED BRASS
stem	BRASS
stem seal	NBR
'O'-rings	NBR
ball seal	NBR
handle	ZAMAK
lockable plate	ZINC-PLATED STEEL

Part Nb	C	E (mm)	F (mm)	F1 (mm)	H (mm)	H1 (mm)	L (mm)	L1 (mm)	M (mm)	ØT (mm)	 (kg)
	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>
0439 04 10	G1/8	8	19	19	59	54	51	27	69	2	.41
0439 07 13	G1/4	12	24	24	60	55	59	31	69	2	.48
0439 10 17	G3/8	12	24	24	60	55	59	31	69	2	.46
0439 13 21	G1/2	15	27	27	62	57	67	34	69	2	.514
0439 18 27	G3/4	16.5	32	38	66	56	80	39	108	2.5	.81
0439 23 34	G1	19	41	46	70	59	94	47	108	3	1.185