



FEATURES:

- ✓ Model 2447 features .531 (13,5mm) Hole Spacing
- ✓ Model 2447A features .500 (12,7mm) Hole Spacing

MATERIALS:

BNC Body: Nickel Tarnish Resistant Plated Brass
 Center Contact: Gold Plated Brass
 Center Contact – Gold over Nickel.
 Dielectric: PTFE
 Gasket: Silicone Rubber

RATINGS:

Operating Voltage: Hands free usage in controlled voltage environments: 500 Vrms maximum. *For CE compliance:* not intended for hand-held use at voltages above 33 Vrms/70 Vdc.

Operating Temperature: -85°F to 329°F (-65°C to +165°C)

Nominal Impedance: 50 Ohms

ORDERING INFORMATION:

Model: 2447 (.531" Mounting Hole Spacing)

Model: 2447A (.500" Mounting Hole Spacing)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.



Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)
 For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com