


# ROHS - COMPLIANT

LTR	REV.	DESCRIPTION	DATE



**NOTES:**

**1. CABLE:**

UL-2725 30AWG(7/0.102 B.C)\*2C INS:SR-PVC ID:0.8±0.05  
 +30AWG(7/0.102 B.C)\*2C INS:SR-PVC ID:0.6±0.05+AL-FOIL/MYLAR  
 +DRAIN WIRE 32AWG(1/0.203 B.C)+BRAID(8/2/0.1 T.C)  
 PVC JACKET OD:4.0±0.15mm COLOR: BEIGE(NK-A03) REV 2.0

**2. CONNECTER:**

- P1:USB A TYPE MALE GOLD FLASH CONTACT,  
NICKEL PLATED SHELL
- P2:USB B TYPE MALE GOLD FLASH CONTACT,  
NICKEL PLATED SHELL
- 3.HOOD: MOULDED TYPE,PVC 45P, COLOR:BEIGE(NK-A03)
- 4.ELECTRICLE TEST:
  - <1>100% OPEN SHORT & MIS WIRE TEST.
  - <2>CONTACT RESISTANCE 3 Ohms MAX.
  - <3>INSULATION RESISTANCE 10M Ohms MIN.
- 5.PACKING:<1>EACH PC / POLYBAG + EAN CODE LABEL & ROHS LABEL  
 <2>EACH CARTON / ROHS LABEL(L\*W=35\*22mm)

**P1**

**P2**

- |         |       |   |        |
|---------|-------|---|--------|
| RED 1   | _____ | 1 | VCC    |
| WHITE 2 | _____ | 2 | -DATA  |
| GREEN 3 | _____ | 3 | +DATA  |
| BLACK 4 | _____ | 4 | GROUND |
| SHELL   | _____ |   | SHELL  |

**2DIRECT GMBH**

Title  
USB A/M - B/M CABLE REV 2.0

Tolerance	Inch	M/M
X	.015	.30
XX	.010	.10
XXX	.005	.05

DWG	P/N	L+T	EAN CODE
170-2688-3	CU0009	5000±50mm	4260113560327
170-2688-2	CU0008	3000±30mm	4260113560310
170-2688-1	CU0007	2000±30mm	4260113560303

Drawn	<b>FANNIE 04/14/06</b>	Customer P/NI
Check		Customer
Engr		Scale NONE Units m/m Third Angle Projection
Dwg No. 170-2688	REV: A	Sheet 1/2