




## Plugs

### MSTF 2



Product	MSTF 2
description	Spring-loaded 2 mm plug, for leads up to 0.5 mm <sup>2</sup> and a maximum outer diameter of 2 mm, suitable to all unsprung 2 mm connections.
article-no. / *colour	9384201xx  <span style="border: 1px solid black; padding: 2px;">Ni</span>
drawing	
technical data	
connection	solder connection
rated voltage <sup>(1)</sup>	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O <sup>(3)</sup>
rated current <sup>(1)</sup> (consider derating curve)	6 A
material plug	brass, nickel plated
housing material	PVC-P
temperature range acc. To IEC61010 <sup>(2)</sup>	-15 °C to +70 °C
standard	IEC 61010

2 mm system

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges

<sup>(3)</sup> Other circuits that are not directly connected to mains

stand: 09.07.2018