

## SC 5 8 OHM

**Art. No. 8005**


**Magnetically shielded 13 mm (0.5") polycarbonate dome driver** for the high-frequency range above 4000 Hz. Balanced [frequency response](#), excellent omnidirectional [sound](#) distribution and high [efficiency](#). Suitable for small sized shielded 2-way combinations for [surround](#) center speakers and multi media systems in conjunction with the shielded fullrange driver [F 8 SC 8 Ohm](#).

**Used in / Accessories:**


[CT CENTER 81](#)

[NANO SAT MK II](#)

[PORTRAIT](#)



[sketch](#)



[frequency- and impedance response](#)

**Technical Data:**

Nominal power handling with high pass	60 W (12 dB/Okt.; 6000 Hz)
Peak power handling with high pass	100 W (12 dB/Okt.; 6000 Hz)
Nominal impedance Z	8 Ohm
Frequency response	1500–22000 Hz
Mean sound pressure level (1 W/1 m)	90 dB
Resonance frequency fs	2000 Hz
Magnetic induction	0,7 T
Magnetic flux	33 μWb
Voice coil diameter	13 mm
Cutout diameter	48 mm
Net weight	0,098 kg

**Similar Products**

[CP 13 4 OHM](#) | [DTW 72 8 OHM](#)

