

Resistance thermometer

Type 412S2RS

Issue 11/21

Applications

Small resistance thermometer for set in with built in connector M12x1

Connection head

built in connector serie 713 M12x1 4-pin

Degree of protection

IP 54 acc. to DIN EN 60529 when closed

Measuring range

0...+100°C

Sensor

1 x Pt 100 F0,3 acc. to DIN EN 60751
in 4-wire-circuit

Protective tube material

1.4571

Protective tube diameter d



ø4 mm

Installment length L

50 mm

Order Example

412S2-E-4L-100-4-50



Subject to change without notice

D- 99331 Geratal OT Geraberg, Gewerbepark 6

Tel: +49 (0) 3677 / 7956-0 // Fax: +49 (0) 3677 / 795 625

E-Mail: info@electrotherm.de

Internet: www.electrotherm.de