

Parallel male thread coupler

Technical characteristics

Technology: "One push" safety system (avoids hose whip)

Operating pressure: 2 to 12 bar

Flow rate at 6 bar: 3530 l/min ($\Delta P = 0,6$ bar)


ID Passage: 10,4 mm

Temperature: -15°C to +70°C

Construction: Polyamide composite body

Highlight: Anti-static, Excellent efficiency, Non scratch



	BSP male thread		Parts Numbers
	G 3/8		ESI 111152EB
	G 1/2		ESI 111153EB
	G 3/4		ESI 111154EB