

RT3FC-B

3 pole female TINY xlr cable connector



Article Variations

Article Name	Details	Packaging
RT3FC-B	Black plated housing, gold plated contacts	Plastic Bag
RT3FC-B-D	Black plated housing, gold plated contacts	BULK
RT3FC-B-W	Black plated housing, gold plated contacts, water resistant boot	Plastic Bag
RT3FC-B-W-D	Black plated housing, gold plated contacts, water resistant boot	BULK

Technical Information

Product

Title	RT3FC-B
Connection Type	XLR

Electrical

Contact Resistance	≤10 mΩ
Insulation Resistance	>1 GΩ
Dielectric Strength	>500 V rms
Rated current per contact	5 A

Mechanical

Cable O.D. Range	2.0-4.5mm
Lifetime	>1000 Mating Cycles
Wiresize	0.22 mm ²
Wiresize	24 AWG

Material	
Ground Contact	Steel
Rubber Spring	Rubber
Latch	Zinc
Chuck	POM
Boot	PC/ABS+TPU
Housing	Zinc
Plastic housing	PA6+30%GF
Jack	Bronze
Ground Contact	Bronze
Tube	Aluminum
Latch	Nickel Plating
Housing	Nickel Plating
Jack	Gold Plating
Ground Contact	Tin and Cer
Tube	Black Plating