

Flashing Light and Siren (red)

Art. no. SG1681

Page 1 of 1



- Can be used in interior areas and protected outer areas
- Separate control of flash light and siren
- Sound pressure: 100 dB (A) @ 1 m
- Protection class: IP34

The flashing light and siren can be mounted inside and outside your building. This combination signalling device is the crucial link of a fully functioning alarm chain. In the event of an alarm, the alarm sounder generates a loud intermittent tone with over 100 dB sound pressure. In addition to the acoustic protection, there is an optical alert from a colored flashing light (frequency: 2 Hz). The alarm sounder and the light can be controlled separately. The robust plastic housing (IP 34) of the combination detector offers protection against environmental influences. To ensure a long service life, you should install the signalling device under cover and protect it from rain. The flashing light and siren are supplied externally with 12V operating voltage. You can choose between three different light colors, according to taste: red (SG1681), yellow (SG1682), and blue (SG1683).

Technical Data:

Dimensions	(WxHxD) 122x73x43 mm
Flashing frequency	2 Hz
Width	122 mm
Housing material	ABS
Height	73 mm
Length	43 mm
Power consumption	2,4 W
Luminous color	Red
Illuminant	4 x Light bulb

Max. operating temperature	50 °C
Min. operating temperature	-10 °C
Installation location	Indoors and protected outdoor areas
Sound pressure	100 dB
IP protection class	34
DC voltage supply	12 V
Power consumption	200 mA