


# USB 3.1 - C Connector

## Features

- Female
- Angled mounting type
- RoHS compliant
- Selective gold 15U"
- Black insulator colour
- 0



## Specification

Current Rating	3 A max.
Voltage Rating	100 VAC
Temperature Range	-30 ... 85 °C
Contact Resistance	40 mOhm max.
Insulation Resistance	100 Mohm min.
Insertion Force	5 ... 20 N
Unmating Force	8 ... 20 N
Durability	10000 Cycles
Shell Material	SUS304, Ni 50u" Plated
Latch Material	SUS301, Ni 50u" Plated
EMI Material	SUS304
Contact Material	C1814
Latch Housing Material	LCP, UL94V-0
Housing Material	LCP, UL94V-0

