


USB 3.0 - A Connector



Features


- 7
- Angled mounting type
- 0
- 8 15u"
- Blue insulator colour
- 0








Specification

Housing Material	PBT, UL94V-0
Terminal Material	Phosphor Bronze / Brass
Shell Material	Stainless Steel
Current Rating	1.5 A max. per Pin
Contact Resistance (Low Level)	30 mOhm max. initial.
Insulation Resistance	1000 MOhm min. initial.
Dielectric Withstanding Voltage	500 VAC
Operating Temperature Min.	-55 °C
Operating Temperature Max.	85 °C

Drawing



RECOMMENDED PCB LAYOUT(TOP VIEW)
GENERAL TOLERANCES:±0.05



Art Nr:

RND 205-01042