



ITEM-NO. (ITEM-NO.)	733-108
Cross section1 (Cross section / mm²)	0.08 - 0.5
Cross section2 (Cross section / AWG)	28 - 20
Strip length (Strip length / mm)	5 - 6
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	6
RM (PIN SPACING / mm)	2.5
P (NO. OF POLES)	8
Height (Height / mm)	11.8
Width (Width / mm)	22.5
Depth (Depth / mm)	17.1
No. of connection Points (No. of connection Points)	8
No. of potentials (No. of potentials)	8
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	3.5
Comment (Comment)	L = (No. of poles x Pin Spacing) + 2,1 mm