



PCB Layout

Technical Data
 Material :
 Contact material :Brass
 Plating:Gold Flash
 Insulator material:Black polyester UL94V-0
 Standard:PA6T+30%G.F

Electrical :
 Current rating:1.0Amps/contact max
 Contact resistance: $\leq 20m\Omega$ /contact
 Insulation resistance: $\geq 1000M\Omega$ at V=100V
 Withstanding voltage:300V AC/minute

Mechanical :
 Soldering temperature: +260°C, 4s max
 UNSPECIFIED TOLERANCE: ± 0.20

$$A = 1.27 * \frac{nP}{2} \pm 0.40$$

$$B = 1.27 * \frac{nP}{2} - 1.27 \pm 0.20$$

Pin Number=4~100

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	DW127R-22-XX-23	
CHECKED			CONNECTOR	
APPROVALS			PART NO.	
TOLEARNCES ARE		30 ^{±0.15}	±0.30	ANGLE
		10 ^{±0.10}	±0.20	UNIT: mm
		5 ^{±0.10}	±0.15	SCALE: 1:1
ECN NO.	REV.	DATE.	DESCRIPTION.	PROJ.
	A		NEW	SHEET 1 OF 1

