



GAFFER 6000 TAPE 'SOUND AND LIGHT'



- Highest quality Gaffer Tape
- Audiovisual applications: ideal for securing and taping up tubes and cables
- High adhesive strength, can be easily peeled off
- Easy to remove, does not leave any residues

| Art. No. | width | length | colour | Pack. | EAN code |
|-------------------|--------|--------|--------|-------|---------------|
| HPX-D6000-1950BK | 19 mm | 50 m | black | 48 | 5425014224337 |
| HPX-D6000-2550BK | 25 mm | 50 m | black | 36 | 5425014224351 |
| HPX-D6000-3850BK | 38 mm | 50 m | black | 24 | 5425014223552 |
| HPX-D6000-5025BK | 50 mm | 25 m | black | 30 | 5425014223491 |
| HPX-D6000-5050BK | 50 mm | 50 m | black | 18 | 5425014223194 |
| HPX-D6000-10050BK | 100 mm | 50 m | black | 12 | 5425014223873 |
| HPX-D6000-1950WH | 19 mm | 50 m | white | 48 | 5425014223774 |
| HPX-D6000-2550WH | 25 mm | 50 m | white | 36 | 5425014224498 |
| HPX-D6000-3850WH | 38 mm | 50 m | white | 24 | 5425014223590 |
| HPX-D6000-5025WH | 50 mm | 25 m | white | 30 | 5425014223538 |
| HPX-D6000-5050WH | 50 mm | 50 m | white | 18 | 5425014223408 |
| HPX-D6000-10050WH | 100 mm | 50 m | white | 12 | 5425014224535 |

Adhesive: natural rubber

Carrier: PE coated cloth

Maximum temperature: 60°C (up to 80°C for short periods)

Tensile strength: 195 N/25 mm

Adhesive strength: 9 N/25 mm

Thickness: 0,30 mm

HPX

Frankrijkstraat 8 | 9140 Temse | Belgium

T 0032 3 710 19 19 | F 0032 3 711 34 64 | info@hpx.eu | www.hpx.eu

