

Dimensions Data

L 线径	W 跨距	H 标高	A 脚长	T 压脚
0.5~3.0mm	5~30mm	5~30mm	3.5±0.2mm	0.75~3.3mm

NOTE:
Contact factory for:
1.Variations of "L" dimension
2.Rated current
3.Variations of "W" dimension
4.Variations OF "H"

PN	Width (W) mm	Height (H+A) mm	(L) mm
CSR-0.8-R010	4	4,5	0,8
CSR-0.8-R020	10	7,5	0,8
CSR-0.8-R030	10	13	0,8
CSR-0.8-R040	10	18,6	0,8
CSR-0.8-R050	10	24,3	0,8
CSR-1.0-R010	5	7,4	1
CSR-1.0-R015	10	9,4	1
CSR-1.0-R020	10	13,84	1
CSR-1.0-R030	10	22,8	1
CSR-1.2-R005	5	5,1	1,2
CSR-1.2-R010	10	9,05	1,2
CSR-1.2-R015	10	15,46	1,2
CSR-1.5-R003	5	5,02	1,5
CSR-1.8-R003	10	5,5	1,8
CSR-1.8-R005	15	8,75	1,8
CSR-1.8-R010	15	23,2	1,8
CSR-1.8-R015	20	35	1,8
CSR-2.0-R003	10	7,7	2
CSR-2.0-R005	15	12,3	2
CSR-2.0-R010	20	27,7	2
CSR-2.5-R003	25	10,1	2,5
CSR-2.5-R005"137"	15	15,2	2,5
CSR-2.5-R005	25	17,9	2,5