

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053072205](#)
Status: **Active**
Overview: [Nano-Fit Power Connectors](#)
Description: Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Single Row, 5 Circuits, Natural, Glow-Wire Capable

Documents:

Drawing (PDF)	Product Specification PS-105300-100-001 (PDF)
3D Model	Application Specification AS-105300-100-001 (PDF)
3D Model (PDF)	Packaging Specification PK-105307-100-000 (PDF)
Product Specification 1053001000-PS-CH-000 (PDF)	Test Summary 1053000000-TS-000 (PDF)
Product Specification 1053001000-PS-ES-000 (PDF)	Test Summary 1053001000-TS-000 (PDF)
Product Specification 1053001000-PS-JP-000 (PDF)	Datasheet (PDF)
Product Specification 1053001000-PS-SK-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

Application tooling part link

Application Tooling Part Link	63824-4600
-------------------------------	------------

General

Product Family	Crimp Housings
Series	105307
Application	Power, Wire-to-Board
Comments	Operating temperature is -40#C to +105#C for tin and -40#C to +115#C for gold
Overview	Nano-Fit Power Connectors
Product Name	Nano-Fit
UPC	889056026628

Physical

Circuits (maximum)	5
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.580/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C, -40° to +115°C

Electrical

Current - Maximum per Contact	6.5A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Application Specification	AS-105300-100-001
Packaging Specification	PK-105307-100-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[105307](#) Series

Mates With

Nano-Fit Vertical Headers [1053092105](#) ,
[1053092205](#) , [1053092305](#) , [1053112105](#) ,
[1053112205](#) , [1053112305](#) , [1054312105](#) ,
[1054312205](#) , [1054312305](#) , [1054312405](#) .
Nano-Fit Right-Angle Headers [1053132105](#)
 , [1053132205](#) , [1053132305](#) , [1054302105](#)
 , [1054302205](#) , [1054302305](#) , [1054302405](#)
 . Nano-Fit Plug Housings [2002772105](#) ,
[2002772205](#)

Use With

Nano-Fit Crimp Terminal [105300](#) . Nano-Fit Pre-Crimped Leads (Gold) [797582129](#) , [797582130](#) . Nano-Fit Pre-Crimped Leads (Tin) [797582139](#) , [797582140](#) . Nano-Fit TPA Retainer [105325](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then

Product Specification

Sales Drawing

Test Summary

1053001000-PS-CH-000, 1053001000-PS-ES-000,
1053001000-PS-JP-000, 1053001000-PS-SK-000,
PS-105300-100-001
SD-105307-100-000
1053000000-TS-000, 1053001000-TS-000

*contained in the Application Tooling
Specification document.*

Global

Description

Product #

Description	Product #
Extraction Tool for Nano-Fit Power Connectors and Crimp Terminals, 20-26 AWG	<u>638244600</u>

This document was generated on 11/10/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[105307-2205](#)