

rotronic

Datenblatt - Fiche technique - Data sheet

11.04.5555




ROLINE Monitorkabel DVI, ST-ST, (24+1) dual link, 5,0m

ROLINE Câble DVI pour écran, (24+1) dual link, 5,0m

ROLINE Monitor Cable, DVI M – DVI M, (24+1) dual link, 5 m

ROHS-COMPLIANT

REV.	DESCRIPTION	DATE
C	ECR #111226-5 ADD LENGTH	12/26/11'



WIRE CONNECTION

P1	WIRE COLOR	P2
1		1
2		2
3		3
3		3
4		4
5		5
6		6
7		7
9		9
10		10
11		11
11		11
12		12
13		13
14		14
15		15
16		16
17		17
18		18
19		19
19		19
20		20
21		21
22		22
23		23
24		24
SHELL	BRAID SHIELDS	SHELL

REMARK:

- CABLE: UL-20276 [28AWG(7/0.127 T.C)*1P+DRAIN WIRE+AL/MY+MYLAR]*7C+28AWG(7/0.127 T.C)*1P+28AWG(7/0.127 T.C)*3C+AL/MYLAR+BRAID SHIELDS(85% T.C) PVC JACKET, OD: 8.6±0.15mm, COLOR:BLACK(NK-K01).
- CONNECTOR:
P1&P2:DVI_D 25P: 24P+KEY MALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL.
- SHIELD: P1&P2 COPPER FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE SHIELDING
- HOOD:
P1&P2:MOLDED TYPE, PVC 45P, COLOR:BLACK(NK-K01)
- FERRITE CORE: (28.5*17.5*9.5) x 2
- TEST REQUEST:
(1) 100% SHORT OPEN & MIS WIRE TEST.
(2) CONTACT RESISITANCE 3 OHMS MAX.
(3) INSULATION RESISITANCE 10M OHMS MIN.
- PACKING: EACH PC / POLY BAG + HEADER CARD(ROLINE, SIZE:205*84mm) + P/N LABEL

Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Rotronic Co., Ltd.

ROLINE DVI Cable, DVI M-M, dual link, 1m, black

Item No.: see the chart

Scale NONE Units m/m Third Angle Projection

REV:C Sheet 1/1

11.04.5521	1000	20	25	7611990198108
11.04.5555	5000	50	10	7611990146062
11.04.5535	3000	30	20	7611990146055
11.04.5525	2000	30	25	7611990146048
P/N	L(mm)	T(mm)	PCS /CTN	BAR CODE NO.