

## Quartz Crystal

HC-49/U3H (low profile)

model	KX - 3HT
frequency	6,0 MHz
holder type	HC-49/U3H
mode	fundamental
operating temperature	-40° ~ + 85°C
frequency tolerance at +25°C	± 30 ppm
temperature tolerance at -40° ~ + 85°C	± 100 ppm
load capacitance $C_L$	16 pF
series resonance $R_1$ max.	80 Ohm
aging (first year)	± 5 ppm
shunt capacitance $C_0$ max.	7 pF
drive level mW	0,1
RoHS	started from date code July, 2005
part no.	12.84246

