


## Within Series Adaptor 34\_SK-50-0-51/199\_N

### Description

Bulkhead adaptor jack/jack  
SK jack (female) / SK jack (female)

For Test & Measurement applications  
Precision adaptor

Interface standard  
Series SK - MIL-STD-348A/323



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	40 GHz
VSWR	DC - 40 GHz ≤ 1.02 + 0.01 f (GHz)

#### Mechanical Data

Number of matings	500
Weight	0.0042 kg

#### Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Interface - SK jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	

Interface - SK jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	

### Related Documents

Outline drawing	DOU-00013638
Mounting hole	DOU-00008731

### Ordering Information

Single package	34_SK-50-0-51/199_NE
----------------	----------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[34\\_SK-50-0-51/199\\_NE](#)