




## Order Code

**MHRJ - 45 - 8P8C - R - 30**

Series \_\_\_\_\_  
 Type \_\_\_\_\_  
 RJ-22, RJ-11, RJ-12, RJ-45, RJ-48  
 Size and Contacts \_\_\_\_\_  
 4P4C (RJ22), 6P4C (RJ11), 6P6C (RJ12),  
 6P6C-OST (RJ12), 8P8C (RJ45),  
 10P10C (RJ48)  
 Cable Style \_\_\_\_\_  
 F = Flat or Oval, R = Round  
 Plating Options \_\_\_\_\_  
 Omit = 50u"  
 6 = 6u", 15 = 15u", 30 = 30u"



## Order Code

**RJ45SRB - QR - R**

Strain Relief Boot \_\_\_\_\_  
 Omit = Bubble Boot (Anti Snag) \_\_\_\_\_  
 QR = Quick Release  
 Colour \_\_\_\_\_  
 LG = Grey, BK = Black, R = Red,  
 G = Green, BL = Blue, Y = Yellow

- Compatible with all FCC specifications
- 50µ" gold plated contacts as standard, but also available in 6, 15 and 30u" plating

- UL94V-0 polycarbonate body
- True knife blade, insulating piercing contacts
- Compatible with standard crimping tools

