

## Test plugs - PAI-4-N GY - 3032871

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test plugs, Color: gray

### Why buy this product

- The small outside diameter of the test socket means that touch-proof safety plugs can also be used
- Reliable contacting of test plugs with a 4 mm diameter in the function shaft



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 529327
Weight per Piece (excluding packing)	1.56 g
Custom tariff number	85366990
Country of origin	Poland

### Technical data

Length	6.5 mm
Width	6 mm

### General

Note	Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in
	Do not plug in while the power is connected
Color	gray
Material	PA
Minimum temperature	-40 °C
Maximum temperature	125 °C

# Test plugs - PAI-4-N GY - 3032871

## Classifications

### eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148

### ETIM

ETIM 3.0	EC000313
ETIM 4.0	EC002255
ETIM 5.0	EC002555

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

### Approvals

---

#### Approvals

EAC

---

#### Ex Approvals

---

#### Approvals submitted

---

### Approval details

EAC
-----

---