

Modlink MSDD front panel interface Data connector insert

USB (form A); RJ45

1 × USB (female/female) form A

1 × RJ45, 8-pole metal, CAT5e (female/female)

Image

Vicarious picture

Technical Data

Operating voltage	SUB-D: max. 125 V AC/150 V DC; RJ4: max. 48 V AC/DC; RJ12: max. 48 V AC/DC; USB: max. 30 V AC/DC; PS2: max. 30 V AC/DC; DVI: max. 40 V AC
Operating current	SUB-D: max. 3 A; RJ45: max. 1 A; RJ12: max. 1 A; USB: max. 1 A; PS2: max. 1 A; DVI: max. 1.5 A
Connection cross section	SUB-D: max. 0.5 mm ² (AWG 20); PS2: max. 0.22 mm ² (AWG 24)
Locking of ports	SUB-D: UNC 4...40 bolt; RJ45: staple; RJ12: staple; USB: snap-in; PS2: snap-in
Specification	SUB-D: (DIN 41652/IEC 60807-1); RJ45: CAT5e (100 MHz · MBit/s); USB: 2.0/Type 2dB (max. 480 Mbit/s)
Mounting depth mounted	SUB-D: approx. 32 mm; RJ45: approx. 32 mm; RJ12: approx. 32 mm; USB: approx. 80 mm; PS2: approx. 32 mm

General data

Shielded	yes
----------	-----

Commercial data

Net weight	50
Weight unit	Gram
Basic unit	pc.
Customs tariff number	85366990
Unit (piece)	1
Minimum order quantity (piece)	1

Communication inserts

RJ45

USB