


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00026	Connector, dc plug, 5.5x2.5xL23 mm, molding style, spring contacts	1	
2	30-00007	Wire, 2C BC, 18 AWG, UL2468, 300V, 80C, 4.4 mm, VW-1, PVC, 87A	1	
3	24-00003	Overmold, PVC	1	black



**Notes:**  
Functionally equivalent components may be substituted

Wiring Diagram	
50-00026	wire color
center	black with stripe
sleeve	black

Revision:	Date:	Description:	Prepared:	Notes:  RoHS compliant  Function test: no open, no short circuit, no intermittent  Description: Cable, 6100 mm, 5.5x2.5x12 mm 50-00026 dc plug to stripped tinned, 18 AWG, 30-00007 wire	<h1>TENSILITY</h1> <p>tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com</p>
A	11/22/2016	Initial release	AW <small>Digitally signed by AW Date: 2018.06.12 10:55:03 -07'00'</small>		
			Verified: AG <small>Digitally signed by AG Date: 2018.06.12 16:21:23 -07'00'</small>		
			Dimensions are in millimeters. Tolerances: X: $\pm 0.5$ mm X.X: $\pm 0.3$ mm X.XX: $\pm 0.05$ mm		
Size:	Part number:				
A	10-02396		Scale: 1:1		Sheet 1 of 1

5

4

3

2

1