



**C1**  
HAR-FLEX 12 POLES FEMALE CONNECTOR WITH STRAIN RELIEF

**C2**  
HAR-FLEX 12 POLES FEMALE CONNECTOR WITH STRAIN RELIEF

HARTING P/N	REVISION	Cable length ( L )
3315 243 010 0004	02	100 ± 3
3315 243 020 0005	02	200 ± 3
3315 243 050 0006	02	500 ± 5
3315 243 060 0006	00	600 ± 10
3315 243 070 0006	00	700 ± 10
3315 243 030 0006	00	300 ± 5
3315 243 005 0006	00	50 ± 3
3315 243 013 0006	00	130 ± 3
3315 243 015 0006	00	150 ± 3
3315 244 255 0006	00	255 ± 3

**WIRING TABLE**

C1	WIRE	C2
1	AWG 30	1
2	AWG 30	2
3	AWG 30	3
-	AWG 30	-
11	AWG 30	11
12	AWG 30	12

**NOTES:**

- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT(500VDC)TEST.
- 2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
- 3.)CABLE SHOULD BE PACKED BY THE PLASTIC BAG,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION) EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
- 4.)WHITE LABEL CONTENT:

DATA CODE  
 HARTING P/N

	All Dimensions in mm	Tech. Character.	Free size tol.	According to production drawing
	All rights reserved	Created by ZHENGL	Inspected by WANGE	Standardisation CHENJU
	Department HCS - CN	Date 2018-07-11		
HARTING Customised Solutions D-32339 Espelkamp		Title Har-Flex 12 Pole,Dul-end,With SR,L=XX MM		
		Type TB	Number 33150002	State Final Release
				Doc-Key / ECM-Nr. 100586793/UGD/000/H 500000137187
				Rev. H Page 1/1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33152430200005](#) [33152430100004](#) [33152430500006](#) [33152430700006](#)