

We measure it.



Mini thermometer

Mini alarm thermometer

Settable min./max. alarm

Permanently attached probe

With a clip for standing up, wall installation or for attachment to clothing



Illustration 1:1

The affordable testo mini thermometer with alarm function is small and handy, but big on performance. The penetration probe has an 80 cm wire and is permanently fixed to the instrument. The probe and the wire can be easily and compactly stored in the instrument.

If individually settable limit values are violated, an audible signal is sounded. The minimum penetration depth of the probe tip should be 20 mm. The alarm thermometer is suitable for the recording of temperature in the air, in soft, powdery substances and in liquids. It is not suitable for use in ovens or fermentation cabinets.

www.testo.com

Technical data / Accessories

Mini alarm thermometer

Mini thermometer, battery included

Part no. 0900 0530



Sensor type

Meas. range	-50 to +150 °C
Accuracy ±1 digit	±1 °C (-10 to +100 °C) ±2 °C (remaining range)
Resolution	0.1 °C (-19.9 to +150 °C) 1 °C (-50 to -20 °C)

General technical data

Oper. temp.	0 to +50 °C
Storage temp.	-20 to +70 °C
Battery type	2 AAA micro batteries
Battery life	100 h
Display	LCD, 1 line
Material/Housing	ABS
Warranty	2 years

Ordering data/Quantity discount

Mini thermometer, from 5 off
Mini thermometer, from 10 off
Mini thermometer, from 25 off
Mini thermometer, from 50 off

Accessories

Part no.

Accessories for measuring instrument

ISO calibration certificate/temperature; for air/immersion probes, calibration point -18°C	0520 0061	
ISO calibration certificate/temperature; for air/immersion probes, calibration point 0°C	0520 0062	