



Dimension (mm)

e	16 ± 1	l	40 ± 2	d	6 ± 0.2 dia
r		g	35 ± 1.5	x	

Polarity : Red dot at anode

Without Colour Corrective Coating :

Remarks:

1. Envelope material: B1
2. RoHS Compliant

Operating Data :

Max. Power Pmax /W		Trigger coil TR	Customer TC
Nom. Power Pnom / W	16	Trigger capacitor Cz /μF	0.22
Max. flashenergy Emax /Ws		Min. trigger voltage Uz min /V	
Nom. flashenergy Enom /Ws	16	Trigger contact S	SCR
Max. anode voltage Uamax /V	350	Flash frequency /Hz	
Nom. anode voltage Uanom /V		Life/Number of flashes /N	10x10p6
Min. anode voltage Uamin /V	150	Repetition rate trep / s	1
Nom. flash capacitor CB / μF		Sec trigger voltage Uz sec / KV	- 4.4
Light reduction after life / %		Unloaded	

Remarks : Functional test in Customer circuit Single Hit SH/EX/T and Double Hit DH/EX/T at 230 VAC