

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301110044](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Pro Yellow Molded Stringlight, 150W, 14/2 SJTW with 2.43m (8.0') Lead 10 Sockets with Guards, Overall Length 30.48m (100.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E112216

General

Product Family Portable Lighting
 Series [130111](#)
 Exclude SD Check Yes
 NEMA Configuration NEMA 1-15
 NEMA Rating Rain Tight
 Outlet None
 Overview [Stringlights](#)
 Product Literature Order No 987650-8055
 Product Name Pro-Yellow
 Type String Lights
 UPC 78172533561

Physical

Cord Length - Primary 2.43m (8.0')
 Cord Length - Secondary 0.61m (2.0')
 Depth N/A
 Duty Commercial
 Guard Included Yes
 Guard Type Polypropylene
 Height N/A
 Length 30.48m (100.0')
 Material - Guard Polypropylene
 Mounting Style Stringer
 Packaging Type Carton
 Socket Construction Molded

Electrical

Bulb Type Incandescent
 Cord Type - Primary 14/2 SJTW
 Lamp Type A21
 Lamp Wattage - Maximum 150W
 Lumens 1500
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 5030



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 ED/108/2014 (17 Dec
 2014)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[130111 Series](#)