

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5034290000](#)
Status: **Active**
Overview: [CLIK-Mate Wire-to-Board Connectors](#)
Description: 1.50mm Pitch, CLIK-Mate Male Crimp Terminal, Tin Plating, 26-30 AWG, Reel

Documents:

3D Model	Product Specification 5031490000-PS-000 (PDF)
3D Model (PDF)	Product Specification 5031490001-PS-000 (PDF)
Drawing (PDF)	Product Specification 5031491000-PS-000 (PDF)
Product Specification 5025780000-PS-000 (PDF)	Product Specification 5031491001-PS-000 (PDF)
Product Specification 5025780001-PS-000 (PDF)	Product Specification 5031491003-PS-000 (PDF)
Product Specification 5025780002-PS-000 (PDF)	Product Specification 5031491004-PS-000 (PDF)
Product Specification 5025780003-PS-000 (PDF)	Application Specification AS-502578-001-001 (PDF)
Product Specification 5025781000-PS-000 (PDF)	Application Specification AS-503149-001-001 (PDF)
Product Specification 5025781000-PS-CHI-000 (PDF)	Application Specification AS-503395-001-001 (PDF)
Product Specification 5025781000-PS-JAP-000 (PDF)	Packaging Specification SPK-503429-001-001 (PDF)
Product Specification 5025781002-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5025781003-PS-000 (PDF)	

General

Product Family	Crimp Terminals
Series	503429
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	CLIK-Mate Wire-to-Board Connectors
Product Name	CLIK-Mate
UPC	883906522988

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	42.000/mg
Packaging Type	Reel
Plating min - Mating	0.406µm
Plating min - Termination	0.406µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.70-1.02mm
Wire Size AWG	26, 28, 30
Wire Size mm ²	0.05-0.13


Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	100V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-502578-001-001, AS-503149-001-001, AS-503395-001-001
Crimp Specification	CS-503429-001-001
Packaging Specification	SPK-503429-001-001
Product Specification	5025780000-PS-000, 5025780001-PS-000, 5025780002-PS-000, 5025780003-PS-000, 5025781000-PS-000, 5025781000-PS-CHI-000, 5025781000-PS-JAP-000, 5025781002-PS-000,



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[503429](#) Series

Use With

[502578](#) CLIK-Mate Housing, [503149](#) CLIK-Mate Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hand Crimp Tool for 1.50mm (.059") Pitch CLIK-Mate Wire-to-Board Crimp Terminal	638251200
FineAdjust Applicator for CLIK-Mate Wire-to-Board Crimp Terminals	639023700

Sales Drawing

5025781003-PS-000, 5031490000-PS-000,
5031490001-PS-000, 5031491000-PS-000,
5031491001-PS-000, 5031491003-PS-000,
5031491004-PS-000
5034290000-SD-000, SD-503429-002-001

T2 Terminator for 639123700
1.50mm (.059")
Pitch CLIK-Mate
Wire-to-Board Crimp
Terminals

This document was generated on 01/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[503429-0000](#)