

## Cat5e Patch Cable with Snagless RJ45 Connectors - 5 m, Grey

Product ID: 45PAT5MGR



This 5-meter Cat5e cable meets or exceeds all Category 5e cable specifications to ensure reliable Ethernet network connections. Plus, the cable features a durable grey PVC jacket that enables you to color code your network cable runs as needed.

### **Snagless RJ45 clips help protect your network connections**

For easier cable runs, the snagless connectors protect the cable's RJ45 clips during installation, making them less likely to snag or break. This ensures a sturdy connection by preventing the cable from becoming loose from the port.

The cable features moulded boots that offer connector strain relief, by stopping the RJ45 connector termination points from bending at sharp angles, and reducing the risk of damage to the cable, which could decrease network performance.

### **100% copper for outstanding value**

Get the highest value for your cable investment with our Cat 5e cables, each one manufactured using high-quality copper conductors.

## **24-gauge wire for high-performance network connection**

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet, using cables that include 24 AWG copper.

## **50-micron gold connectors provide peak conductivity**

Rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

The 45PAT5MGR is backed by StarTech.com's lifetime warranty for guaranteed reliability.

### Certifications, Reports and Compatibility



### Applications

- Designed for use with Fast Ethernet networks
- Connect between computers, hubs, switches, print servers and patch panels
- Connect a workstation to an RJ45 wall outlet

### Features

- Prevent cable damage with moulded RJ45 connectors that also offer strain relief
- Create secured connections with snagless clips that protect the connectors during installation
- Guaranteed reliability with a lifetime warranty
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Type	Snagless
	Fire Rating	CM Rated
	Number of Conductors	4 pair UTP
<b>Performance</b>	Cable Rating	CAT5e - 350 MHz
<b>Connector(s)</b>	Connector A	1 - RJ-45 Male
	Connector B	1 - RJ-45 Male
<b>Physical Characteristics</b>	Cable Length	5 m [16.4 ft]
	Color	Gray
	Conductor Type	Stranded Copper
	Product Length	5 m [16.4 ft]
	Product Weight	174 g [6.1 oz]
	Wire Gauge	24 AWG
<b>Packaging Information</b>	Package Height	20 mm [0.8 in]
	Package Length	330 mm [13 in]
	Package Width	255 mm [10 in]
	Shipping (Package) Weight	194 g [6.8 oz]
<b>What's in the Box</b>	Included in Package	1 - 5 m Cat5e Patch Cable - Gray

Product appearance and specifications are subject to change without notice.