


113A.10C 113A.C - Chromed adjustable wrenches



- Good access to the button = easy setting.
- Non-protruding moving jaw at maximum capacity.
- Pre-adjustment of jaw opening thanks to millimetric gradation.
- Right-hand button rotation.
- Range from 4" to 24".
- Presentation: chromed body and polished head faces.

A [mm]: 30

B [mm]: 69,5

C x C1 [mm]: 21,5 x 28,5

C1 [mm]: 28,5

E [mm]: 9,0

E maxi [mm]: 9

E1 [mm]: 15,5

E2 [mm]: 9,5

E3 [mm]: 12,7

E4 [mm]: 10,0

L [mm]: 255

L1 [mm]: 29

[g]: 480