

Han 3A-AK-Dichtung, Kappe o. glatt



Part number	09 20 003 5408
Specification	Han 3A-AK-Dichtung,Kappe o. glatt
HARTING eCatalogue	https://b2b.harting.com/09200035408

Identification

Category	Hoods/Housings
Series of hoods/housings Han A [®]	
Type of hood/housing	Protection cover
	for bulkhead mounted housings
Description of hood/	for bulkhead mounted housings for surface mounted housings
Description of hood/ housing	

Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications
Details	for mounted female insert or for mounted Han-Brid [®] insert

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44 IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Material properties

REACH SVHC substances No

Specifications and approvals

Approvals	DNV GL	
-----------	--------	--

Commercial data

Packaging size	10
Net weight	4.62 g
Country of origin	Romania
European customs tariff number	85389099