

FEATURES

- High impact resistant thermoplastic
- Knob finish - Matt
- Body material - Burnished steel
- Standard colour - Black knob
- Options Available with or without a 90° locking rest position

RS PRO M12 Index Plunger, 45mm Long

RS Stock No.: 237-491



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE

For positioning operations on a range of equipment. Available in both standard form and flat plate version for fixing to thinner panels by either screws or rivets. Available with or without rest positions. Rest position achieved by rotating head 90 degrees to enable plunger to remain in its retracted position. Made from burnished steel with hardened steel plunger with a plastic technopolymer black knob. Flat plate made from zinc plated steel

General Specifications

Type	Index Plunger
Body Material	Burnished steel
Thread Size	M12
Applications	Ideal for applications where precision positioning is needed, such as rotary indexing heads. Clamping of adjustable elements; Positioning of work pieces; Latching of mechanisms


Mechanical Specifications

Length	45mm
Ball Diameter	6mm

Approvals

Compliance/Certifications	RoHS
----------------------------------	------





Part No.	A	B	C	D	E	Thread size	Plunger diameter (mm)	Rest position
478359	21	51	5	17	5	M10x1.0	5	No
237491	25	45	5	10	6	M12x1.5	6	No
478721	25	61	6	20	6	M12x1.5	6	No
237429	31	54	6	12	8	M16x1.5	8	No
478769	31	75	8	26	7	M16x1.5	8	No
237570	25	45	5	10	6	M12x1.5	6	Yes
237388	31	54	6	12	8	M16x1.5	8	Yes