



			1		
	Part Number:		DRAWN	8/10/2017	
	MOOO	4204-1	CJ	0/10/2017	
	MO09		CHECKED	8/14/2017	
			P.D.	0/11/2017	
Ī	Description:	enser Microphone	APPROVED	8/14/2017	
	l Electret Conde		C.E.		

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View




Side View



Bottom View





Items	Specifications	Conditions				
Directivity	Omnidirectional					
Sensitivity	-42 ± 2	dB				
Frequency Range	50 ~ 16,000	Hz		REVISION HISTOR	Υ	
Rated Voltage	4.5	V	REV	DESCRIPTION	DATE	APPROVED
Voltage Range	1 ~ 10	V		Released from Engineering	10/21/2013	J.S.
Output Impedance	2,200	Ω	1	Add Pin Dimensions, update to new template, voltage range changed	8/14/2017	C.E.
Max. Rated Current	0.5	mA		NOTES		
Storage Temperature	-25 ~ +70	°C	1) All dimensions are in mm unless otherwise noted			
Operating Temperature	-20 ~ +60	°C	2) All tolerances are ± 0.5 mm unless otherwise noted			
Signal to Noise Ratio	60	dB	3) All parts meet RoHS			
Mount Type	Thru Hole			4) Subject to change or redrawn	without notice	
Connection Method	PC Pins					