



**May not be suitable for all Medical and Aerospace applications.  
Contact Mallory Sonalert to discuss your application.**

**NO CIRCUITRY**

Oscillation Frequency (Hz)	2048
Operating Voltage (Vp-p)	1.25 ~ 2.5
Rated Voltage (Vp-p)	1.5
Current Consumption Max. (mA)	18 at Rated Voltage
Sound Pressure Level Min. (dB)	80 at 10cm at Rated Voltage
Coil Resistance ( $\Omega$ )	$42 \pm 5$
Operating Temperature ( $^{\circ}\text{C}$ )	-20 ~ +70
Storage Temperature ( $^{\circ}\text{C}$ )	-30 ~ +80
Housing	PPO plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	1.2
Options	For other options contact factory

**Dimensions:** (units: mm)**ROHS Compliant**

After Code Date 2017/06/13



Before Code Date 2017/06/12

**Packaging:** Parts are supplied in tube (40 per tube).