

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0533531071](#)

Status: **Active**

Overview:

Description: SlimStack Board-to-Board Connector, 0.80mm Pitch, Floating Series, Plug, 7.00 or 8.00mm Mated Height, 10 Circuits, Vertical, without Boss

General

Product Family	PCB Headers
Series	53353
Application	Board-to-Board, Signal
Overview	slimstack_fine_pitch_smt_board_to_board_connectors
Product Name	SlimStack
Series Name	0.80 Floating
UPC	822348161430

Physical

Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Durability (mating cycles max)	30
Glow-Wire Capable	No
Lock to Mating Part	None
Mated Height	7.00mm, 8.00mm
Mated Width	5.10mm, 7.20mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	300.100/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.80mm
Polarized to PCB	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Material Info

Reference - Drawing Numbers

Product Specification	PS-52465-010-001
Sales Drawing	SD-53353-003, SD-53353-004

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[53353](#) Series

Mates With

[52465](#) , [52588](#) PCB Receptacle

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[53353-1071](#)