

# Han F+B-HCC-M25 blue



Part number	19 15 513 1701
Specification	Han F+B-HCC-M25 blue
HARTING eCatalogue	https://b2b.harting.com/19155131701

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods/Housings
Series	Han <sup>®</sup> F+B
Type of hood/housing	Cable to cable housing

#### Version

Locking type	Screw locking
Version	Top entry
Cable entry	1x M25
Field of application	Connector for food+beverage industry
Details	Cleaning: For cleaning with high pressure lances, a cleaning distance > 30 cm is recommended in order to avoid mechanical damage to the connector's exterior parts.
	Strain relief:A suitable strain relief is required to enable the F+B connectorto resist the stress caused e.g. by the daily cleaning of the machinery. DIN VDE 0100-520: 2013-06 defines the stress relief for a connector depending on the outer diameter of the cable.

### Technical characteristics

Limiting temperature	-40 +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP67 in locked position
	IP6K9K acc. to ISO 20653

### Material properties

Material (hood/housing)	Polypropylen
Roughness of the surface	≤1.12 µm



## Material properties

Colour (hood/housing)	Blue
Material (seal)	Silicone
Colour (seal)	Blue
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No
EG1935/2004	compliant

## Specifications and approvals

	Ecolab Topactive 200
	Ecolab Topactive 500
	Ecolab Topax 66
Approvala	Ecolab Topactive OKTO
Approvals	Ecolab Topax 990
	FDA 21 CFR 177.1520
	FDA 21 CFR 177.2600
CE	Yes

### Commercial data

Packaging size	1
Net weight	24 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors